






# AVENTICS™ ED07 | ED12



Manuals | Anleitungen | Manuels | Istruzioni | Instrucciones

| Series                          | Product Type (EN/DE/FR/IT/ES)  | Download Manual  |
|---------------------------------|--|--|
| <b>ED07 controlled analogue</b> | Proportional pressure regulator, controlled analogue<br>Proportional-Druckregelventil, analog gesteuert<br>Régulateur de pression proportionnel, analogique contrôlé<br>Valvola riduttrice di pressione proporzionale, analogico controllato<br>Válvula reguladora de presión proporcional, analógico controlado | <br><a href="#">doc. R414001671</a>   |
| <b>ED12 controlled analogue</b> |  | <br><a href="#">doc. R414002587</a>   |
| <b>ED07 / ED12 EtherCAT</b>     | Proportional pressure regulator, with fieldbus<br>Proportional-Druckregelventil, mit Feldbus<br>Régulateur de pression proportionnel, avec bus de terrain<br>Valvola riduttrice di pressione proporzionale, con bus di campo<br>Válvula reguladora de presión proporcional, con bus de campo                     | <br><a href="#">doc. R414014377</a>  |
| <b>ED07 / ED12 Profinet</b>     |  | <br><a href="#">doc. R414014550</a> |
| <b>ED07</b>                     | Base plates for assembling<br>Grundplatten zur Montage<br>Embases pour montage<br>Piastre base per il montaggio<br>Placas base para montaje  | <br><a href="#">doc. R414006606</a> |