

8

7

6

5

4

3

2

1

GENERAL NOTES (UNLESS OTHERWISE SPECIFIED)

REVISIONS						
REV	ECN	DESCRIPTION OF CHANGE	DRAWN	CHKD	APVD	DATE

D

D

Sensor Terminals


Sensor Types:

- CMF010
- CMF025
- CMF050
- CMF100
- CMF200
- CMF300 (excluding CMF300A)
- CMF400
- CNG050
- T025 F025 H025
- T050 F050 H050
- T075 F100 H100
- T100 F200 H200
- T150 F300 H300

Transmitter:

3500
IS CONNECTOR

	C	D	
	2	2	
VDC+	4	4	VDC-
RS485A	6	6	RS485B
	8	8	
	10	10	
	12	12	
	14	14	
	16	16	
	18	18	
	20	20	
	22	22	
	24	24	
	26	26	
	28	28	
	30	30	
	32	32	



CUSTOMER SUPPLIED CABLE
 MAXIMUM LENGTH:
 1000 ft (300m) OF 18 AWG(0.8 mm²)
 300 ft (100m) OF 22 AWG(0.35 mm²)

C

C

B

B

A

A

COPYRIGHT 2005 MICRO MOTION, INC.
ALL RIGHTS RESERVED

ITEM	DESCRIPTION	PART OR REF. NO.	MATL. OR MFR.	QTY.
		MICRO MOTION, INC. BOULDER, COLORADO		
		WIRING, CORE TO 3500		
DRAWN	NAME	DATE	SIZE	DWG. NO.
CHKD.	JLA	1/5/04	D	EW-20001931
APVD.	JLA	1/5/04	SCALE NONE	DO NOT SCALE DRAWING SHEET 1 OF 1

8

7

6

5

4

3

2

1