

8

7

6

5

4

3

2

1

GENERAL NOTES (UNLESS OTHERWISE SPECIFIED)

REVISIONS						
REV	ECN	DESCRIPTION OF CHANGE	DRAWN	CHKD	APVD	DATE

D

D

C

C


Sensor Mounted
Core Processor

Sensor Types:


DS600

Transmitters:

1700R
2700R



CUSTOMER SUPPLIED CABLE
 MAXIMUM LENGTH:
 1000 ft (300m) OF 18 AWG(0.8 mm²)
 300 ft (100m) OF 22 AWG(0.35 mm²)



VALID FOR APPROVAL CODES:
 - Micro Motion Standard General Purpose
 - Cenelec/ATEX

ITEM	DESCRIPTION	PART OR REF. NO.	MATL. OR MFR.	QTY.
			MICRO MOTION, INC. BOULDER, COLORADO	
	THIRD ANGLE PROJECTION		WIRING, DS600 CORE TO 1700R/2700R	
DRAWN	SAD	10/31/02	SIZE DWG. NO.	REV.
CHKD.	JLA	11/5/02	D EW-20000623	A
APVD.	JLA	11/5/02	SCALE NONE DO NOT SCALE DRAWING	SHEET 1 OF 1

COPYRIGHT 2002 MICRO MOTION, INC.
 ALL RIGHTS RESERVED

8

7

6

5

4

3

2

1

A

A