

MODEL 1700/2700 WITH NON INCENDIVE FIELDBUS IN HAZARDOUS LOCATION

(WARNING: SUBSTITUTIONS OF COMPONENTS MAY IMPAIR INTRINSIC SAFETY)

Refer to Model Number on 1700/2700 transmitter tag for specific Hazardous Location

*Increased Safety Outputs:
No Display
Ex de [ib] IIC T5

With Display
Ex de [ib] IIB + H2 T5

FNICO PER EN60079-27:2006 NON INCENDIVE FIELDBUS PARAMETER	
Um	33 Vdc
I _{max}	380 mA
P _{max}	5.32 W
Ci	0.0002µF
Li	0.0µH

*Flameproof Outputs:
No Display
Ex d [ib] IIC T5

With Display
Ex d [ib] IIB + H2 T5

Note: Hazardous area classification on an integrally mounted 1700/2700 transmitter can be limited by hazardous area classification of the sensor. Refer to sensor tag.

