


F

GB

D

Repère	DESIGNATION du sachet	DESIGNATION of kit	BEZEICHNUNG der Ersatzteil-Packung	CODE
	ELECTROVANNE STANDARD 10VA - 5W (LV.N) PIECES MOBILES	SOLENOID VALVE STANDARD 10VA - 5W (LV.N) MOBILE PARTS	MAGNETVENTIL STANDARD 10VA - 5W (LV.N) BEWEGLICHE TEILE	976 00 010
1	1 Noyau standard	1 Standard plunger	1 Standard-Anker	
2	1 Ressort de rappel	1 Spring	1 Rückholfeder	
3	1 Joint nitrile	1 Nitrile seal	1 NBR Dichtungsring	
4	1 Joint nitrile	1 Nitrile seal	1 NBR Dichtungsring	
	ENSEMBLE BUSE Ø 2	KIT NOZZLE Ø 2	DÜSENSATZ Ø 2	976 00 012
5	1 Buse Ø 2 mm	1 Nozzle Ø 2 mm	1 Düse	
6	1 Ecrou de blocage	1 Nut	1 Mutter	
7	1 Cache buse	1 Protection cap	1 Verschlussdeckel	
8	2 Joints nitrile	2 Nitrile seals	2 NBR Dichtungsringe	
	ELECTROVANNE FAIBLE CONSOMMATION 1,5 W (LV.Z) PIECES MOBILES	SOLENOID VALVE LOW CONSUMPTION 1,5 W (LV.Z) MOBILE PARTS	MAGNETVENTIL mit geringer Leistungsaufnahme 1,4 W (LV.Z) BEWEGLICHE TEILE	976 00 009
1	1 Noyau standard	1 Standard plunger	1 Standard-Anker	
2	1 Ressort de rappel	1 Spring	1 Rückholfeder	
3	1 Joint nitrile	1 Nitrile seal	1 NBR Dichtungsring	
4	1 Joint nitrile	1 Nitrile seal	1 NBR Dichtungsring	
	ENSEMBLE BUSE Ø 1	KIT NOZZLE Ø 1	DÜSENSATZ Ø 1	976 00 011
5	1 Buse Ø 1 mm	1 Nozzle Ø 1 mm	1 Düse	
6	1 Ecrou de blocage	1 Nut	1 Mutter	
7	1 Cache buse	1 Protection cap	1 Verschlussdeckel	
8	2 Joints nitrile	2 Nitrile seals	2 NBR Dichtungsringe	
9	1 CONNECTEUR	1 ELECTRICAL CONNECTOR	1 STECKANSCHLUSS	976 00 013
10	1 BOBINE : Consulter le tableau général des bobines PR-PNE 14600	1 COIL : See general coil leaflet PR-PNE 14600	1 SPULE : Siehe entsprechende Spulentabelle PR-PNE 14600	



I

E

NL

Marca Rif Positie	COMPOSIZIONE della serie	DESIGNACION del conjunto	BESCHRIJVING onderdelenet	CODICE CODIGO CODE
	ELETTROVALVOLA STANDARD 10VA - 5W (LV.N) PARTI MOBILI	ELETTROVALVOLA STANDARD 10VA - 5W (LV.N) PLEZAS MOVILES	STANDAARD ELEKTROKLEP 10VA - 5W (LV.N) PLUNGER MET	976 00 010
1	1 Nucleo standard	1 Nucleo standard	1 Standard plunjer	
2	1 Molla di ritorno	1 Resorte de retorno	1 Vaer	
3	1 O-ring Nitrile	1 Junta de Nitrilo	1 O-ring	
4	1 O-ring Nitrile	1 Junta de Nitrilo	1 O-ring	
	COMPLESSO SEDE Ø 2	CONJUNTO TORNILLO DE REGLAJE Ø 2	ZITTINGSET Ø 2	976 00 012
5	1 Sede Ø 2 mm	1 Tornillo de reglaje Ø 2 mm	1 Zitting Ø 2 mm	
6	1 Dado di bloccaggio	1 Fuerca de bloqueo	1 Bergmoer	
7	1 Tappo	1 Tapa de proteccion	1 Beschermdop	
8	2 O-ring Nitrile	2 Juntas de Nitrilo	2 O-ringen	
	ELETTROVALVOLA A BASSO CONSUMO 1,5 W (LV.Z) PARTI MOBILI	ELETTROVALVOLA DE BAJO CONSUMO 1,5 W (LV.Z) PIEZAS MOVILES	SPOEL LAAG VEVMOGEN 1,5 W (LV.Z) PLUNGER MET	976 00 009
1	1 Nucleo standard	1 Nucleo standard	1 Standard plunjer	
2	1 Molla di ritorno	1 Resorte de retorno	1 Vaer	
3	1 O-ring Nitrile	1 Junta de Nitrilo	1 O-ring	
4	1 O-ring Nitrile	1 Junta de Nitrilo	1 O-ring	
	COMPLESSO SEDE Ø 1	CONJUNTO TORNILLO DE REGLAJE Ø 1	ZITTINGSET Ø 1	976 00 011
5	1 Sede Ø 1 mm	1 Tornillo de reglaje Ø 1 mm	1 Zitting Ø 1 mm	
6	1 Dado di bloccaggio	1 Fuerca de bloqueo	1 Bergmoer	
7	1 Tappo	1 Tapa de proteccion	1 Beschermdop	
8	2 O-ring Nitrile	2 Juntas de Nitrilo	2 O-ringen	
9	1 CONNETTORE	1 CONNECTOR	1 STEKERKAP	976 00 013
10	1 Bobina : Consultare la tabella generale delle bobine PR-PNE 14600	1 Bobina : Consultar la tabla general de bobinas PR-PNE 14600	1 Spoel : zie spoelenlijst PR-PNE 14600	

COMMANDE : pour votre commande, nous préciser le N° de code correspondant au sachet dont le contenu est indivisible
ORDERING : when ordering, please specify code No. of «kits»; the parts cannot be supplied separately.
BESTELLUNG : es werden nur Teile zusammengefasst gemäss festgelegter Code-Nr. geliefert.

ORDINE : per ordinare precisare il numero di codice della serie di ricambi desiderata (fornibili solo serie complete).
PEDIDO : precisar el nº del código del conjunto cuyo contenido es indivisible.
BESTELLING : onderdelen zijn uitsluitend per set leverbaar, op de verpakking is het code nummer vermeld.