


Fluid Automation Solutions for Press Room and Metal Stamping

www.asconumatics.com



EMERSON
Industrial Automation



Numatics delivers intelligently designed, reliable, long-lasting automation solutions. Our fluid power products provide press rooms and metal stamping facilities with their pneumatic components of choice.

Presenting Numatics solutions

The standout choice for metal stamping

For automation of metal stamping operations worldwide, end users as well as machine builders and original equipment manufacturers (OEMs) can turn to Numatics. Our comprehensive pneumatic components packages make it easy and cost-effective to troubleshoot production faults and reduce downtime.

Applied with confidence

Use ultra-reliable Numatics fluid power products in manufacturing segments ranging from automotive and transportation to appliances, agricultural equipment, and many more.

For example, they're the components of choice in automotive metal stamping presses, de-stackers, oil re-apply stations, die bolsters, press transfer equipment, and end-of-press racking units. That includes body manufacturing and assembly of:

- Stamped parts
- Hoods
- Doors
- Door hinges
- Deck lids
- Hemmers
- Roof systems

Exceptional reliability

Numatics is a leading manufacturer of innovative, reliable pneumatics and motion control products. Our offerings have rock-solid quality and durability to stand up to punishing service in press rooms and other challenging areas. For example, Numatics valves feature our signature spool and sleeve design, proven to provide maximum reliability and performance. Users report that our products deliver longer mean time between failure (MTBF) than competitive brands. Result: the industry's longest service life.

Unique fieldbus electronics platform

Numatics offers easy, cost-effective solutions for digital I/O and valve automation with technology found only in our G3 electronics. Choose localized or distributed architecture. Get fewer nodes to commission, plus fewer points of failure via minimized I/O points and shorter cord sets. Optimize rack space for PLCs and scanner cards. Sharply lower your overhead costs.

Each G3 module has a unique integrated graphic display for simple, intuitive commissioning, plus a host of exclusive features for fast diagnostics during production. Our auto recovery module (ARM) option safeguards configuration data, enabling quick module replacement and machine availability. And G3 is compatible with all major industrial protocols — DeviceNet™, EtherNet/IP, Profibus® DP, PROFINET®, CC-Link IE Field™, and more.

Added benefits

Count on Numatics for a highly diverse product offering, providing exceptional performance in products from fieldbus electronics and extended-life suction cups to valves and tubing. You also get unsurpassed savings, due to long product lives and lower maintenance costs. Plus special advantages such as Numasizing — which correctly sizes your pneumatic components for reduced energy consumption.

In addition, our unbeatable technical support outdoes the competition in attentive customer support and speedy response. While our unmatched availability and delivery mean you get short lead times, solid supply chain support, and the industry's best quick-shipment program: Numatics Express.



Numatics FRL Assemblies

Modular high-flow filters, regulators and lubricators (FRLs) that are designed for automotive-type applications. They are robust and easy to assemble. End plates are available for easy extraction of the entire FRL assembly.




Numatics Delta Series Premium Filters

Numatics Delta Series offers high flow compressed air filtration solutions for metal stamping type applications. Products include water separators, particulate filters and various grades of coalescing filter elements.



Numatics Cylinders

Numatics air cylinder product lines meet all national and international standards. Combining robust construction with a multitude of optional features allow our cylinders to perform in the most demanding applications. Numatics POGO cylinder design provides through-rod vacuum capability resulting in fewer components while promoting a cleaner, less complicated, press application.



Numatics G3 Fieldbus Manifolds

The revolutionary Numatics G3 electronics platform provides centralized or distributed valve and I/O architecture for maximum cost-effectiveness. A unique graphic display on each module allows effortless configuration. It also enables ultra-easy diagnostics, so users can quickly find and fix any faults that may occur during production. Result: far less downtime for critical stamping press operations.



Numatics Automotive-Style Vacuum Cups

These wear-resistant, automotive-style suction cups feature a reinforced design specifically created for vehicle manufacturing applications. Special patterns on each cup's underside help prevent slippage on oily surfaces.



Numatics Directional Control Valves

Choose pneumatic directional control valves with ultra-high flow rates, for greater throughput and reduced maintenance costs. These advanced valves are ideal for automation and piloting applications across a wide range of press shop and general machinery applications.

Numatics Extended-Life Vacuum Cups

Ultra-robust suction cups with soft, tapered sealing lips are proven to deliver up to 10 times normal service life. During placement on workpiece, cups deliver high suction force with optimum dampening effect. Results: greater wear resistance — with longer runs for stamping presses, less production downtime, and fewer cup replacements.

Global Contacts

www.asconumatics.com

ASCO Headquarters (U.S.A.)
Tel: 800-972-ASCO (2726) or
+1 973-966-2000
info-valve@asco.com

Numatics (U.S.A.)
Tel: 888-Numatics (686-2842) or
+1 248-596-3200
InsideSales@numatics.com

- ★ Global Headquarters
- Regional Headquarters
- Manufacturing & Key Offices



Other Worldwide Locations

Australia	(61) 2-9-451-7077	Italy	(39) 02-356931
Brazil	(55) 11-4208-1700	Japan	(81) 798-65-6361
Canada	(1) 519-758-2700	Mexico	(52) 55-5809-5640
China	(86) 21-3395-0000	Netherlands	(31) 33-277-7911
Czech Republic	(420) 235-090-061	Singapore	(65) 6556-1100
Dubai - UAE	(971) 4-811-8200	South Korea	(82) 2-3483-1570
France	(33) 1-47-14-32-00	Spain	(34) 942-87-6100
Germany	(49) 7237-9960	Turkey	(90) 216-577-3107
India	(91) 44-39197300	United Kingdom	(44) 1695-713600

ASCO
numatics™

ASCO Numatics and Right Now are trademarks of Automatic Switch Co. The Emerson logo is a trademark and service mark of Emerson Electric Co. DeviceNet is a trademark of ODVA. EtherNet/IP is a trademark of ODVA. ControlNet International under license by ODVA. PROFIBUS and PROFINET are registered trademarks of Profibus International. CC-Link IE Field is a trademark or registered trademark of the CC-Link Partner Association (CLPA) or related company. All other brands may be trademarks of their respective holders.

© 2013 ASCO Numatics. All rights reserved.
Printed in the U.S.A.