



OMNI 2000 Cleaning Systems – Models 1620 and 1620 RI

The *OMNI 2000* cleaning system by Branson is a fully-configured ultrasonic cleaning and rinsing system with a built-in dryer. Also available, as an option, is a rust inhibitor station in the second rinse tank. The equipment incorporates quality workmanship and materials without including unnecessary extras.

The *OMNI 2000* offers a full range of hard-working features, while occupying only a fraction of the floor space of comparable systems. All controls are mounted in a convenient control box and operate at 24 volts for safety.

CLEANING

Precision cleaning is accomplished in the first chamber. This chamber is equipped with Branson Series 7000 industrial 40 kHz ultrasonic components and thermostatically-controlled heat. A recirculating pump and filter system to continuously remove particulate material is standard.

RINSING

The OMNI-2000 includes two heated rinse tanks in a cascade arrangement.

Rinse water overflows from tank three into tank two. This counter-flowing feature provides excellent rinsing while substantially reducing water consumption.

Tank two includes ultrasonic components as standard to assure that all soils and cleaning chemistry are driven from blind holes and crevices before the dry cycle.

RUST INHIBITING OPTION

As an option, the user may choose to use the second rinse tank as a rust inhibitor dip prior to drying. This model, 1620-RI, is useful when cleaning steel components. The valving associated with this system allows easy conversion from a single overflow rinse back to a dual tank cascade rinse in seconds if your process changes.

DRYING

The drying station utilizes both elevated temperature and rapid air movement to produce dry parts. The chamber is furnished with a 3" vent duct to facilitate moist air removal.

Ultrasonic Cleaning

FEATURES & BENEFITS


- Clean, rinse, and dry in a single unit
- Small footprint minimizes floor space needs
- Low voltage controls for safety
- Standard filtration to extend cleaning bath life
- Ultrasonics on rinse tank for superior performance
- Convenient working height
- Durable stainless steel construction
- Easy access to routine maintenance components
- Convenient control panel for easy operation
- Recessed work surface for fluid spill containment
- Automation interface port for transport systems (e.g., Branson TDR)
- Rust inhibition option for steel parts

OPTIONS


- Wash Tank Surface Sparger
- Oil Removal Package (Coalescer, Ultrafiltration)
- DI Water Heater
- DI Water Treatment System
- Automated Material Handling (TDR)
- Rotating Baskets
- Series 8500 Advanced Power Supply
- Hinged Power Cover for Dryer

Specifications

Working tank size:	16" x 20" x 16" D
Process tank material:	316L bright annealed
Drain sizes:	3/4" NPT
Cleaning tank temperature:	Ambient to 160° F
Recirculation flow rate:	1-3 GPM
Filter retention:	10 microns
Ultrasonic output:	1000 watts/tanks
Dryer heat:	6,000 watts
Dryer airflow:	550 cfm
Dryer temperature:	250° F maximum
Input voltage:	208-240V, AC, 35 amps, 3 phase



Basic Design



NOTE: Dimensions are in inches.

Americas

Branson Ultrasonics Corp.
41 Eagle Road
Danbury, CT 06813-1961
T: 800-732-9262
F: 203-796-2250
www.bransonultrasonics.com

Europe

Branson Ultraschall
Niederlassung der Emerson
Technologies GmbH & Co. OHG
Waldstrasse 53-55
63128 Dietzenbach, Germany
T: +49-6074-497-0
F: +49-6074-497-199
www.branson.eu

Asia

Branson Ultrasonics (Shanghai) Co., Ltd.
758 Rong Le Dong Road
Song Jiang, Shanghai, PRC, 201613
T: 86-21-3781-0588
F: 86-21-5774-5100
www.branson-china.com

OMNI 1620 © Branson Ultrasonics Corporation 2016
The Emerson logo is a trademark and service mark of Emerson Electric Co. Revised and printed in the U.S.A. 1/16
PC-DAN-0012-12