


FISHER

Regulators


Fisher Family of Farm Taps

Natural Gas Distribution:


- Farm Tap
- Small City Gate / District Station
- Town Border Station
- Monitors



627 Series



EZR (1-INCH)




630



EZR (2 x 1-INCH)

Natural Gas Production:

- First Stage High Pressure Cut
- Gas Gathering
- Underground Storage
- Farm Tap



	Maximum Inlet Pressure	Outlet Pressure Range	Maximum Capacity	Type Number
	1,050 psig 73 bar	6-inches w.c. to 700 psig 15 mbar to 49 bar	875,000 scfh 23 500 m ³ /h(n)	EZR
Quick Selection	1,500 psig 103 bar	3 to 500 psig 0,21 to 34,5 bar	130,000 scfh 3480 m ³ /h(n)	630
	2,000 psig 140 bar	5 to 500 psig 0,34 to 34,5 bar	179,000 scfh 4800 m ³ /h(n)	627

Specifications




Construction Materials:

Body: Ductile Iron, Steel
Casings: Aluminum, Ductile Iron or Steel
Trim: Aluminum or Stainless Steel
Seat Material: Nitrile, Flourelastomer or Nylon
Body Size: 3/4, 1 or 2-inch
End Connections: NPT, 150RF, 300RF, 600RF or PN 16/25/40
Other Constructions Available: NACE, Internal Relief and Monitors



Construction Materials:

Body: Cast Iron or Steel
Casings: Cast Iron or Steel
Trim: Brass or Stainless Steel
Seat Material: Nitrile, Flourelastomer or Nylon
Body Size: 1 or 2-inch
End Connections: NPT, 150RF, 300RF or 600RF
Other Constructions Available: NACE



Construction Materials:

Body: Cast Iron (2x1 only) or Steel
Bonnet: Steel
Trim: Stainless Steel
Elastomers: Nitrile or Flourelastomer
Body Size: 1, 1-1/4 or 2-inch
End Connections: NPT, 125RF, 150RF, 250RF, 300RF or 600RF

