


# Sonifier Cell Disruptor




## Disruptor Horns

A. 1/2" Horn  
B. 3/4" Horn

### OVERVIEW

Horns (probes) transmit ultrasonic energy into a solution. The dimensions of the horn and the output control setting determine the amount of amplitude (tip movement) and degree of ultrasonic activity in the liquid. Generally, the smaller the tip diameter, the higher the amplitude. Larger tip diameters have less amplitude but can accommodate larger volumes. All Sonifier horns and tips are fabricated from titanium. Please note the charted amplitude ratings and liquid volumes when selecting horns.

A step horn with a threaded body enables the attachment of various screw-on accessories, such as a continuous flow cell. Tapped horn ends enable attachment of microtips. Tapped horns are supplied with removable flat tips.



Model SFX550 shown

Flow-thru horn compatible with SFX250 and SFX550, Digital 250 and 450, Analog 250 and 450.

# Sonifier Cell Disruptor

**NOTE:**

High gain horns can't be used with screw-on accessories as they provide higher amplitude.

Exponential horns have lower tip amplitude but can withstand higher tip loading. Best suited for applications requiring the compressing of solids such as powders and tissue.

\*Available with graduated depth scale on horn tip, part number 101-147-036.

\*\* Amplitudes quoted are total peak-to-peak movement in microns as measured on positions 1 and 10 of the output control

+ Replaceable flat tip, 1/4-20 thread, part number 101-148-013

++ Replaceable flat tip, 1/4-28 thread, part number 101-147-024

**STEP HORNS WITH THREADED BODY**



Tip Diameter	3/8" (9.5mm)	1/2" (13mm)	1/2" (13mm)	3/4" (19mm)
Tip Conf.	Solid	Tapped +	Solid	Solid
Intensity	Very High	High	High	Medium
Ampl. Range**	36-240	21-145	21-145	9.5-63
Volume (Liquid)	5-300 mL	10-500 mL	10-500 mL	25-1000 mL
Part Number	101-147-039	101-147-037*	101-147-038	101-147-043

**HIGH GAIN HORNS\***



Tip Diameter	3/4" (19mm)	1" (25.4mm)
Tip Conf.	Solid	Solid
Intensity	Medium	Low
Ampl. Range**	19-130	6.3-40.5
Volume (Liquid)	25-1000 mL	50-2000 mL
Part Number	101-147-035R	101-147-076

**EXPONENTIAL HORNS\***



Tip Diameter	1/2" (13mm)	1/2" (13mm)
Tip Conf.	Tapped++	+ Solid
Intensity	Medium	Medium
Ampl. Range**	10-65	10-65
Volume (Liquid)	10-500 mL	10-500 mL
Part Number	101-147-040	101-147-041

**Americas**

Branson Ultrasonics Corp.  
41 Eagle Road  
Danbury, CT 06813-1961  
T: 203-796-0400  
F: 203-796-9838  
www.Emerson.com/Branson

**Europe**

Branson Ultraschall  
Niederlassung der Emerson  
Technologies GmbH & Co. OHG  
Waldstrasse 53-55  
63128 Dietzenbach, Germany  
T: +49-6074-497-0  
F: +49-6074-497-199  
www.Emerson.com/Branson

**Asia**

Branson Ultrasonics (Shanghai) Co., Ltd.  
758 Rong Le Dong Road  
Song Jiang, Shanghai, PRC, 201613  
T: 86-21-3781-0588  
F: 86-21-5774-5100  
www.Emerson.com/Branson