

We believe regulators should be seen and not heard.

Fisher® EZH and Tartarini™ FL Series Regulators

Minimal noise. Maximum technology. Our Noise Attenuation Technology provides efficient source treatment, meeting a broad range of application requirements. It's one of many reasons to choose an EZH or FL for your installation.

- No bleed technology
- Reliable shutoff
- Integral slam-shut
- Operates up to 1500 psig / 103 bar inlet pressure
- Offers spring-open alternative maximizing uptime
- Source treatment noise attenuation
 - Easy field retrofit; no need to bury
 - Robust design
 - Highly efficient



For more information download a PDF brochure at delivr.com/1aqen_qr or by scanning the QR code with your smart phone.


EMERSON[™]
Process Management

D351947X012 Product Advertisement © 2011 Emerson Process Management Regulator Technologies, Inc. All rights reserved. Fisher, Tartarini, Emerson Process Management, and the Emerson Process Management design are marks of the Emerson Process Management group of companies.

EMERSON. CONSIDER IT SOLVED.™